## APC Products Limited

www.pailclosures.com

<u>com</u> Tel: 905-457-0887

## APC-25-AG-MV PRODUCT SPECIFICATION

DESCRIPTION	APC-25-AG-MV ANTI-GLUG + MICROPOROUS VENT CLOSURE
PART NUMBER	APC-25-AG-MV
PART DRAWING	AD9-2-AG-MV Rev 5 APC-2-AG-MV Anti Glug Closure with Microporous Vent
CLOSURE SIZE	38 mm (1.5 inch) neck thread diameter, 6 threads per inch 44 mm (1.8 inch) body height extended
COVER OPENING	2.56 inch (65 mm) cover beaded rim outside diameter 0.24 to 0.28 inch cover bead height See AD9-2.4 Rev 5 APC-25 & APC-4L Cover Opening drawing
CLOSURE WEIGHT	28 Grams +/- 1
MATERIAL & COLOR	FDA approved virgin resins CAP – high density polyethylene, white BODY – EVA co-polymer low density polyethylene, natural VENT – Polytetrafluoroethylene (PTFE), manufacturer specs available
TAMPER EVIDENCE	CAP – 4 tabs must be broken to lift 2 bails BODY – internal diaphragm with pull ring molded into spout
INSTALLATION	Same as APC-25 installation See APC web site <u>www.pailclosures.com/installation</u>
PERFORMANCE *	Hydrostatic leak test target: 30 kPa (4.5 psi) water for 30 minutes. Eight tabs fold inward as closure is opened. Flow control reduces glugging, splashing and clean-up. Microporous vent acts as filter which passes gas but blocks liquid, and should be sealed to perform the above hydrostatic test.
PTFE COMPATIBILITY	Testing must be done to determine if packaged product is compatible with PTFE microporous membrane vent. PTFE material is hydrophobic, not oleophobic. Adverse effects may include blocking of vent holes or wetting through. PTFE manufacturer's specs available upon request.
APPLICATION *	The closure is designed for UN Packing Group II and III applications up to 30 kPa subject to performance and product compatibility testing. Do not use for hot fill applications or UN Packing Group I applications. Keep bottom of nested closure above the liquid fill level.
CONTROL OF CHANGE	Specifications are subject to change. APC-25-AG-MV buyers on record will be notified.
PERFORMANCE * PTFE COMPATIBILITY APPLICATION * CONTROL OF	<ul> <li>See APC web site <u>www.pailclosures.com/installation</u></li> <li>Hydrostatic leak test target: 30 kPa (4.5 psi) water for 30 minutes. Eight tabs fold inward as closure is opened. Flow control reduces glugging, splashing and clean-up. Microporous vent acts as filter which passes gas but blocks liquid, and should be sealed to perform the above hydrostatic test.</li> <li>Testing must be done to determine if packaged product is compatible with PTFE microporous membrane vent. PTFE material is hydrophobic, not oleophobic. Adverse effects may include blocking of vent holes or wetting through. PTFE manufacturer's specs available upon request.</li> <li>The closure is designed for UN Packing Group II and III applications up to 30 kPa subject to performance and product compatibility testing. Do not use for hot fill applications or UN Packing Group I applications. Keep bottom of nested closure above the liquid fill level.</li> <li>Specifications are subject to change. APC-25-AG-MV buyers on record</li> </ul>

\* These product specifications are intended as a guide only. Closures are manufactured under an ISO 9001:2015 management program. Sample closures are available for product testing. It is the responsibility of the buyer and filler to ensure the closure meets the product compatibility and performance requirements for both regulated and non-regulated packaging applications.

Exhibit 9-25-AG-MV

Rev 6 7-2024